Spring Plungers • headed, with ball and internal hexagon 22030.0935



Product Description

Spring plungers can be used for locating or for applying pressure, as a detent or for ejection. Precise screwing depth due to head.

Material

Body

Free cutting steel, blackened

Ball

· Ball-bearing steel, hardened

Spring

Stainless steel

Assembly

Respect dimension I_3 for M 4 / M 5.

Characteristic

Standard spring load: no marking





Heavy spring load

Standard spring load

More information


Notes


Special types on request. Spring plungers are specially tested for spring range and forces.

References

Thread lock on request, please refer to appendix - Technical Data -Calculation of indexing resistance, please refer to appendix - Technical Data -

Drawing





Size M4+M5


Size M6-M12

Order information

Dimensions					WS Stroke	Spring load ¹⁾		ß	Ĭ	Art. No.	
d1	d ₂	d ₃	I ₁	I ₂		S	F1 ~	F ₂ ~	max.		
[mm]					[mm]	[mm]	[N]		[°C]	[g]	
free cutting ste	eel, standa	ard spring loa	ad		· · · · ·						
M12	8	18	26	19	6	2.5	26	49	250	21	22030.0935

1) statistical average value

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 23.01.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.