

## Adjustable Flat Tension Levers • Stainless steel

EH 24441.



### Product Description

Adjustable flat tension levers are used when the swivel range is limited or a specific lever position is required.

Adjustable flat tension levers are characterised by their low construction height and are particularly suitable for use in restricted spaces or when the lever should not overhang..

### Material

#### Lever

- Zinc die-cast, plastic coated, black, similar to RAL 9005, matt structure
- Zinc die-cast, plastic coated, silver, similar to RAL 9006, matt structure

#### Inner parts

- Stainless steel 1.4305


#### Covering

- Plastic, black
- Plastic, light grey



### Operation



By lifting the lever the serrations are disengaged. The lever can be positioned by the serrations. On releasing the lever, the serrations are automatically re-engaged.

### Drawing



### Order information

Dimensions												Art. No.	
d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub> H7	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	l <sub>2</sub>	t min.	min.	max.		
[mm]										[°C]			[g]
with female thread – picture 1, black													
32	M 8	–	16	29.5	2	2.5	41.5	120	14	-30	80	192	<a href="#">24441.0205</a>
32	M10	–	16	29.5	2	2.5	41.5	120	14	-30	80	183	<a href="#">24441.0210</a>
32	M12	–	16	29.5	2	2.5	41.5	120	14	-30	80	181	<a href="#">24441.0215</a>
40	M12	–	23	42.0	4	4.0	56.0	145	22	-30	80	403	<a href="#">24441.0220</a>
40	M16	–	23	42.0	4	4.0	56.0	145	22	-30	80	381	<a href="#">24441.0225</a>

Dimensions										 min. max.			Art. No.
d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub> H7	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	l <sub>2</sub>	t min.	[°C]		[g]	
[mm]													
with female thread – picture 1, silver													
32	M 8	–	16	29.5	2	2.5	41.5	120	14	-30	80	192	<a href="#">24441.0305</a>
32	M10	–	16	29.5	2	2.5	41.5	120	14	-30	80	183	<a href="#">24441.0310</a>
32	M12	–	16	29.5	2	2.5	41.5	120	14	-30	80	181	<a href="#">24441.0315</a>
40	M12	–	23	42.0	4	4.0	56.0	145	22	-30	80	403	<a href="#">24441.0320</a>
40	M16	–	23	42.0	4	4.0	56.0	145	22	-30	80	381	<a href="#">24441.0325</a>
with smooth bore – picture 2, black													
32	–	8	16	29.5	2	2.5	41.5	120	14	-30	80	188	<a href="#">24441.0250</a>
32	–	10	16	29.5	2	2.5	41.5	120	14	-30	80	181	<a href="#">24441.0255</a>
40	–	12	23	42.0	4	4.0	56.0	145	22	-30	80	395	<a href="#">24441.0260</a>
40	–	16	23	42.0	4	4.0	56.0	145	22	-30	80	380	<a href="#">24441.0265</a>
with smooth bore – picture 2, silver													
32	–	8	16	29.5	2	2.5	41.5	120	14	-30	80	188	<a href="#">24441.0350</a>
32	–	10	16	29.5	2	2.5	41.5	120	14	-30	80	181	<a href="#">24441.0355</a>
40	–	12	23	42.0	4	4.0	56.0	145	22	-30	80	395	<a href="#">24441.0360</a>
40	–	16	23	42.0	4	4.0	56.0	145	22	-30	80	380	<a href="#">24441.0365</a>

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.  
<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.