


Flat Knurled Nuts • DIN 467

EH 24760.



Product Description


- Material
- Steel, blackened, quality 5
 - Stainless steel 1.4305, dull blasted

More information

Notes

Knurling pitch and knurling depth may differ from DIN.

Drawing




Order information

Dimensions						Art. No.
d ₁	d ₂	d ₃	h	k		
[mm]						
Steel						
M 3	12	6	3	2.5	2.1	24760.0030
M 4	16	8	4	3.5	5.1	24760.0040
M 5	20	10	5	4.0	9.4	24760.0050
M 6	24	12	6	5.0	17.0	24760.0060
M 8	30	16	8	6.0	32.0	24760.0080
M10	36	20	10	8.0	61.0	24760.0100
M12	40	22	12	10.0	92.0	24760.0120¹⁾
Stainless steel						
M 3	12	6	3	2.5	2.1	24760.0230
M 4	16	8	4	3.5	5.1	24760.0240
M 5	20	10	5	4.0	9.4	24760.0250
M 6	24	12	6	5.0	17.0	24760.0260
M 8	30	16	8	6.0	32.0	24760.0280
M10	36	20	10	8.0	61.0	24760.0300

¹⁾ DIN standards do not include these dimensions.

Application example



Compliance

For detailed compliance information please select the desired article number.