# Ball-Ended Thrust Screws • headless, ball protected against rotating 22700.0661



# **Product Description**

Ball-ended thrust screws can also be used for clamping, tightening or supporting of non-parallel

The flat-faced, movable ball enables a flat load transmission.

#### Material

#### Ball

· Ball-bearing steel, hardened

Heat-treated steel, 1200 ±100 N/mm<sup>2</sup>

#### More information

Ball protected against rotating. Special types on request.


#### References

Thread lock on request, please refer to appendix - Technical Data -

#### **Further products**

- · Ball-Ended Thrust Screws, headless, flatfaced ball
- Ball-Ended Thrust Screws, headless, with fine-pitch thread
- Ball-Ended Thrust Screws, headless, flatfaced ball and hexalobular socket

## **Drawing**





# **Order information**


d <sub>1</sub>	Dimensions d <sub>1</sub>				Load capacity for static load <sup>1)</sup> max.	ă	Art. No.
[mm]				[mm]	[kN]	[g]	
flat-faced ball, bearing surface plain, Heat-treated steel							
M16	20	10.7	12	8	36	22	22700.0661

<sup>1)</sup> Statements on load capacity are not valid for the stainless steel type.

Erwin Halder KG

Page 1 of 2 Published on: 3.2.2024

# **Application example**



# Compliance

#### **RoHS** compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

# Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 23.01.2024.

# **Contains Proposition 65 substances**



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Erwin Halder KG

# **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2

Published on: 3.2.2024