

## Adjustable Clamping Levers · inner parts from stainless steel, with female thread

### EH 24390.



#### Product Description

Adjustable clamping levers with rust-proof inner parts. Suitable for multiple applications, e.g. medical environments, chemical industry, and so on.

#### Material

##### Lever

- Zinc die-cast, plastic coated, orange similar to RAL 2004, matt structure
- Zinc die-cast, plastic coated, black, similar to RAL 9005, matt structure

##### Threaded part

- Stainless steel 1.4305

##### Inner parts

- Stainless steel 1.4305

#### Operation


**By lifting the lever** the serrations are disengaged. The lever can be positioned by the serrations. On releasing the lever, the serrations are automatically re-engaged.

#### More information


#### Notes


The threaded portion can be exchanged.

#### Drawing




#### Order information

Dimensions										Art. No.
d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	l <sub>2</sub>	t ≥		
[mm]										
orange										
13	M 3	10.0	24.5	4.0	3.5	30.5	30	7	26	24390.0032
13	M 4	10.0	24.5	4.0	3.5	30.5	30	9	25	24390.0036
14	M 5	10.0	24.5	4.0	3.0	35.0	45	8	33	24390.0111
14	M 6	10.0	24.5	4.0	3.0	35.0	45	8	33	24390.0121
18	M 8	13.5	31.0	6.5	3.0	45.0	62	10	67	24390.0321
22	M 8	16.0	36.0	8.0	3.5	52.0	74	14	112	24390.0411
22	M10	16.0	36.0	8.0	3.5	52.0	74	14	109	24390.0421
25	M10	19.0	43.0	11.0	4.0	63.0	89	17	175	24390.0511
25	M12	19.0	43.0	11.0	4.0	63.0	89	17	171	24390.0521
30	M12	23.0	50.5	12.0	5.0	76.0	108	22	286	24390.0611
30	M16	23.0	50.5	12.0	5.0	76.0	108	22	269	24390.0621
black										
13	M 3	10.0	24.5	4.0	3.5	30.5	30	7	26	24390.0034
13	M 4	10.0	24.5	4.0	3.5	30.5	30	9	25	24390.0038
14	M 5	10.0	24.5	4.0	3.0	35.0	45	8	33	24390.0114
14	M 6	10.0	24.5	4.0	3.0	35.0	45	8	33	24390.0124
18	M 8	13.5	31.0	6.5	3.0	45.0	62	10	67	24390.0324
22	M 8	16.0	36.0	8.0	3.5	52.0	74	14	112	24390.0414
22	M10	16.0	36.0	8.0	3.5	52.0	74	14	109	24390.0424

Dimensions										Art. No.
d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	l <sub>2</sub>	t ≥		
[mm]										
25	M10	19.0	43.0	11.0	4.0	63.0	89	17	175	<a href="#">24390.0514</a>
25	M12	19.0	43.0	11.0	4.0	63.0	89	17	171	<a href="#">24390.0524</a>
30	M12	23.0	50.5	12.0	5.0	76.0	108	22	286	<a href="#">24390.0614</a>
30	M16	23.0	50.5	12.0	5.0	76.0	108	22	269	<a href="#">24390.0624</a>

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 23.01.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure  
<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.