

조절 클램핑 레버 · 스텐레스 스틸 재질의 내부부품, 숫나사 타입
EH 24390.



제품 설명

녹 방지 재질의 내부 부품이 있는 타입. 의료기 산업이나 화학 산업 등 다양한 분야에 사용 가능.

재질

레버

- 아연 다이 캐스트, 플라스틱 코팅, RAL 2004와 유사한 주황색, 무광
- 아연 다이 캐스트, 플라스틱 코팅처리, 검은색, RAL 9005와 유사, 무광 처리

내부 부품

- 스텐레스 스틸 1.4305

나사

- 스텐레스 스틸 1.4305

작동


레버를 들면, 내부의 톱니가 풀린다. 톱니에 따라 핸들은 어느 위치로든 회전되고, 핸들을 놓으면, 톱니가 자동적으로 다시 맞물려진다.

더 많은 정보


참조


스크류 부분을 교체 가능.

그림




주문 정보

d ₁	d ₂	l ₁	d ₃	치수 h ₁ [mm]	h ₂	h ₃	h ₄	l ₂	 [g]	제품 번호.
주황색										
13	M 4	12	10,0	24,5	4,0	3,5	30,5	30	27	24390.0010
13	M 4	16	10,0	24,5	4,0	3,5	30,5	30	30	24390.0014
13	M 4	20	10,0	24,5	4,0	3,5	30,5	30	28	24390.0018
13	M 4	25	10,0	24,5	4,0	3,5	30,5	30	28	24390.0022
13	M 4	32	10,0	24,5	4,0	3,5	30,5	30	29	24390.0026
14	M 5	12	10,0	24,5	4,0	3,0	35,0	45	36	24390.0041
14	M 5	16	10,0	24,5	4,0	3,0	35,0	45	36	24390.0051
14	M 5	20	10,0	24,5	4,0	3,0	35,0	45	37	24390.0061
14	M 5	25	10,0	24,5	4,0	3,0	35,0	45	38	24390.0071
14	M 5	32	10,0	24,5	4,0	3,0	35,0	45	38	24390.0081
14	M 5	40	10,0	24,5	4,0	3,0	35,0	45	39	24390.0086
14	M 6	12	10,0	24,5	4,0	3,0	35,0	45	37	24390.0131
14	M 6	16	10,0	24,5	4,0	3,0	35,0	45	37	24390.0141
14	M 6	20	10,0	24,5	4,0	3,0	35,0	45	38	24390.0151
14	M 6	25	10,0	24,5	4,0	3,0	35,0	45	39	24390.0161
14	M 6	32	10,0	24,5	4,0	3,0	35,0	45	40	24390.0171
14	M 6	40	10,0	24,5	4,0	3,0	35,0	45	41	24390.0181
14	M 6	50	10,0	24,5	4,0	3,0	35,0	45	43	24390.0191
18	M 8	16	13,5	31,0	6,5	3,0	45,0	62	74	24390.0331
18	M 8	20	13,5	31,0	6,5	3,0	45,0	62	76	24390.0341

치수										제품 번호.
d ₁	d ₂	l ₁	d ₃	h ₁	h ₂	h ₃	h ₄	l ₂		
[mm]										
18	M 8	25	13,5	31,0	6,5	3,0	45,0	62	77	24390.0351
18	M 8	32	13,5	31,0	6,5	3,0	45,0	62	79	24390.0361
18	M 8	40	13,5	31,0	6,5	3,0	45,0	62	81	24390.0371
18	M 8	50	13,5	31,0	6,5	3,0	45,0	62	84	24390.0381
18	M 8	63	13,5	31,0	6,5	3,0	45,0	62	89	24390.0391
22	M10	20	16,0	36,0	8,0	3,5	52,0	74	128	24390.0441
22	M10	25	16,0	36,0	8,0	3,5	52,0	74	130	24390.0451
22	M10	32	16,0	36,0	8,0	3,5	52,0	74	134	24390.0461
22	M10	40	16,0	36,0	8,0	3,5	52,0	74	138	24390.0471
22	M10	50	16,0	36,0	8,0	3,5	52,0	74	143	24390.0481
22	M10	63	16,0	36,0	8,0	3,5	52,0	74	148	24390.0486
22	M10	80	16,0	36,0	8,0	3,5	52,0	74	157	24390.0491
25	M12	25	19,0	43,0	11,0	4,0	63,0	89	205	24390.0541
25	M12	32	19,0	43,0	11,0	4,0	63,0	89	209	24390.0551
25	M12	40	19,0	43,0	11,0	4,0	63,0	89	215	24390.0561
25	M12	50	19,0	43,0	11,0	4,0	63,0	89	222	24390.0571
25	M12	63	19,0	43,0	11,0	4,0	63,0	89	232	24390.0581
25	M12	80	19,0	43,0	11,0	4,0	63,0	89	240	24390.0591
30	M16	32	23,0	50,5	12,0	5,0	76,0	108	348	24390.0641
30	M16	40	23,0	50,5	12,0	5,0	76,0	108	357	24390.0651
30	M16	50	23,0	50,5	12,0	5,0	76,0	108	370	24390.0661
30	M16	63	23,0	50,5	12,0	5,0	76,0	108	386	24390.0671
30	M16	80	23,0	50,5	12,0	5,0	76,0	108	407	24390.0681
검정색										
13	M 4	12	10,0	24,5	4,0	3,5	30,5	30	27	24390.0012
13	M 4	16	10,0	24,5	4,0	3,5	30,5	30	30	24390.0016
13	M 4	20	10,0	24,5	4,0	3,5	30,5	30	28	24390.0020
13	M 4	25	10,0	24,5	4,0	3,5	30,5	30	28	24390.0024
13	M 4	32	10,0	24,5	4,0	3,5	30,5	30	29	24390.0028
14	M 5	12	10,0	24,5	4,0	3,0	35,0	45	36	24390.0044
14	M 5	16	10,0	24,5	4,0	3,0	35,0	45	36	24390.0054
14	M 5	20	10,0	24,5	4,0	3,0	35,0	45	37	24390.0064
14	M 5	25	10,0	24,5	4,0	3,0	35,0	45	38	24390.0074
14	M 5	32	10,0	24,5	4,0	3,0	35,0	45	38	24390.0084
14	M 5	40	10,0	24,5	4,0	3,0	35,0	45	39	24390.0089
14	M 6	12	10,0	24,5	4,0	3,0	35,0	45	37	24390.0134
14	M 6	16	10,0	24,5	4,0	3,0	35,0	45	37	24390.0144
14	M 6	20	10,0	24,5	4,0	3,0	35,0	45	38	24390.0154
14	M 6	25	10,0	24,5	4,0	3,0	35,0	45	39	24390.0164
14	M 6	32	10,0	24,5	4,0	3,0	35,0	45	40	24390.0174
14	M 6	40	10,0	24,5	4,0	3,0	35,0	45	41	24390.0184
14	M 6	50	10,0	24,5	4,0	3,0	35,0	45	43	24390.0194
18	M 8	16	13,5	31,0	6,5	3,0	45,0	62	74	24390.0334
18	M 8	20	13,5	31,0	6,5	3,0	45,0	62	76	24390.0344
18	M 8	25	13,5	31,0	6,5	3,0	45,0	62	77	24390.0354
18	M 8	32	13,5	31,0	6,5	3,0	45,0	62	79	24390.0364
18	M 8	40	13,5	31,0	6,5	3,0	45,0	62	81	24390.0374
18	M 8	50	13,5	31,0	6,5	3,0	45,0	62	84	24390.0384
18	M 8	63	13,5	31,0	6,5	3,0	45,0	62	89	24390.0394
22	M10	20	16,0	36,0	8,0	3,5	52,0	74	128	24390.0444
22	M10	25	16,0	36,0	8,0	3,5	52,0	74	130	24390.0454
22	M10	32	16,0	36,0	8,0	3,5	52,0	74	134	24390.0464
22	M10	40	16,0	36,0	8,0	3,5	52,0	74	138	24390.0474
22	M10	50	16,0	36,0	8,0	3,5	52,0	74	143	24390.0484
22	M10	63	16,0	36,0	8,0	3,5	52,0	74	148	24390.0489
22	M10	80	16,0	36,0	8,0	3,5	52,0	74	157	24390.0494
25	M12	25	19,0	43,0	11,0	4,0	63,0	89	205	24390.0544
25	M12	32	19,0	43,0	11,0	4,0	63,0	89	209	24390.0554
25	M12	40	19,0	43,0	11,0	4,0	63,0	89	215	24390.0564
25	M12	50	19,0	43,0	11,0	4,0	63,0	89	222	24390.0574
25	M12	63	19,0	43,0	11,0	4,0	63,0	89	232	24390.0584
25	M12	80	19,0	43,0	11,0	4,0	63,0	89	240	24390.0594

d ₁	d ₂	l ₁	d ₃	치수		h ₂	h ₃	h ₄	l ₂	 [g]	제품 번호
				h ₁	[mm]						
30	M16	32	23,0	50,5		12,0	5,0	76,0	108	348	24390.0644
30	M16	40	23,0	50,5		12,0	5,0	76,0	108	357	24390.0654
30	M16	50	23,0	50,5		12,0	5,0	76,0	108	370	24390.0664
30	M16	63	23,0	50,5		12,0	5,0	76,0	108	386	24390.0674
30	M16	80	23,0	50,5		12,0	5,0	76,0	108	407	24390.0684

적용 예



규정 준수

RoHS 준수

납 성분 포함 - 예외조항 6a / 6b / 6c 준수

0.1% w/w 이상 함유된 SVHC 물질 포함

납 성분 포함 - 2024년 1월 23일 SVHC 목록

식수안전 및 독성물질 관리법 물질 포함



납은 노출로 인해 압과 생식 기능에 해를 끼칠 수 있습니다
<https://www.P65Warnings.ca.gov/>

분쟁 광물 포함하지 않음

이 제품은 탄탈륨, 주석, 금 또는 텅스텐 등 민주 공화국 또는 인접 국가에서 "분쟁 광물"로 지정된 물질을 포함하지 않습니다.